

FP600s

Prysmian Fire Resistant Armoured Power Cable
BS 7846-F120. 600/1000 V.



The ultimate fire resistant, armoured cable for power and control of emergency, life safety and fighting systems used in buildings

Cores (qty)	Nominal cross sectional area (mm ²)	Approximate overall diameter Ø (mm)	Cable Glands	Cable Fixings	Enhanced Fire Resisting Joints
2	4	20.1	422LSF-55	370CG-04	EFRZHMPJ-3
2	6	20.2	422LSF-55	370CG-04	EFRZHMPJ-3
2	10	22.9	422LSF-55	370CG-05	EFRZHMPJ-4
2	16	24.2	422LSF-55	370CG-05	EFRZHMPJ-4
2	25	26.7	KA493-56	370CG-06	EFRZHMPJ-4
2	35	30.3	422LSF-56	370CG-06	EFRZHMPJ-4
2	50	30.0	422LSF-56	370CG-06	EFRZHMPJ-4
2	70	32.8	422LSF-57	370CG-07	EFRZHMPJ-5
2	95	35.2	422LSF-57	370CG-07	EFRZHMPJ-5
2	120	38.7	422LSF-58	370CG-08	EFRZHMPJ-5
2	150	41.5	422LSF-58	370CG-08	EFRZHMPJ-5
2	185	46.3	422LSF-59	370CG-09	EFRZHMPJ-5
2	240	50.9	422LSF-59	370CG-09	EFRZHMPJ-5
2	300	55.3	422LSF-61	370CG-10	EFRZHMPJ-6
2	400	60.5	422LSF-61	370CG-11	EFRZHMPJ-6

Prysmian

A Brand of Prysmian Group

RELIABILITY
AT ITS CORE

PRYSMIAN

FP

FIRE PERFORMANCE CABLES

Cores (qty)	Nominal cross sectional area (mm ²)	Approximate overall diameter Ø (mm)	Cable Glands	Cable Fixings	Enhanced Fire Resisting Joints
3	4	20.2	422LSF-55	370CG-05	EFRZHMPJ-3
3	6	20.2	422LSF-55	370CG-04	EFRZHMPJ-3
3	10	24.4	422LSF-55	370CG-05	EFRZHMPJ-4
3	16	25.6	422LSF-55	370CG-06	EFRZHMPJ-4
3	25	29.5	422LSF-56	370CG-06	EFRZHMPJ-4
3	35	32.3	422LSF-56	370CG-07	EFRZHMPJ-4
3	50	32.2	422LSF-56	370CG-07	EFRZHMPJ-4
3	70	35.2	422LSF-57	370CG-07	EFRZHMPJ-5
3	95	40.1	422LSF-58	370CG-08	EFRZHMPJ-5
3	120	43.4	422LSF-58	370CG-08	EFRZHMPJ-5
3	150	48.5	422LSF-59	370CG-09	EFRZHMPJ-5
3	185	52.4	422LSF-61	370CG-09	EFRZHMPJ-6
3	240	57.5	422LSF-61	370CG-11	EFRZHMPJ-6
3	300	62.6	422LSF-61	370CG-12	EFRZHMPJ-6
3	400	68.8	422LSF-63	370CG-13	EFRZHMPJ-7
4	4	20.2	422LSF-55	370CG-04	EFRZHMPJ-4
4	6	21.3	422LSF-55	370CG-05	EFRZHMPJ-4
4	10	26.0	KA493-56	370CG-06	EFRZHMPJ-4
4	16	27.8	KA493-56	370CG-06	EFRZHMPJ-4
4	25	32.1	422LSF-56	370CG-07	EFRZHMPJ-4
4	35	35.3	422LSF-57	370CG-07	EFRZHMPJ-5
4	50	36.4	422LSF-57	370CG-08	EFRZHMPJ-5
4	70	40.5	422LSF-58	370CG-08	EFRZHMPJ-5
4	95	44.3	422LSF-58	370CG-08	EFRZHMPJ-5
4	120	49.4	422LSF-59	370CG-09	EFRZHMPJ-5
4	150	53.6	422LSF-61	370CG-10	EFRZHMPJ-6
4	185	58.8	422LSF-61	370CG-11	EFRZHMPJ-6

Prysmian

A Brand of Prysmian Group

RELIABILITY
AT ITS CORE

PRYSMIAN

FP

FIRE PERFORMANCE CABLES

FIRE PERFORMANCE

Cores (qty)	Nominal cross sectional area (mm ²)	Approximate overall diameter Ø (mm)	Cable Glands	Cable Fixings	Enhanced Fire Resisting Joints
4	240	64.4	422LSF-61	370CG-13	EFRZHMPJ-7
4	300	69.9	422LSF-63	370CG-14	EFRZHMPJ-7
4	400	78.6	422LSF-64	370CG-15	EFRZHMPJ-8
5	4	22.1	422LSF-55	370CG-05	EFRZHMPJ-4
5	6	23.7	422LSF-55	370CG-05	EFRZHMPJ-4
5	10	28.8	KA493-56	370CG-06	EFRZHMPJ-4
5	16	31.3	422LSF-56	370CG-07	EFRZHMPJ-4
5	25	34.7	422LSF-57	370CG-07	EFRZHMPJ-5
5	35	38.2	422LSF-57	370CG-08	EFRZHMPJ-5

Prysmian

A Brand of Prysmian Group

RELIABILITY
AT ITS CORE

