

Installation Procedure for Fitting the Old Style CSM Oval Port Bracket for the New Spine

Product application

This instruction details how to attach an old version of the oval port CSM bracket to the base of a small or medium node when a new one-piece spine is used.



Precautions and Warnings

- ! This guide is only valid for products purchased from or approved by Prysmian Group.
- ! During this procedure all local Health & Safety statutory regulations must be adhered to.
- ! This installation should only be carried out by suitably trained competent persons.

1. Flat Head
screwdriver

PN: N/A



Remove Spine from the base

Step 1



The tab in the spine must be pushed out so that the spine is released from the base.

Step 2



Using a flat-head screwdriver, gently push the tab out through the hole in the base. When pushing the tab pull the spine away from the base.

Step 3



When you can see the whole tab the spine has been pulled out far enough. It does not matter if you go too far and the spine is completely removed.

Attaching the CSM bracket

Step 4

Place the CSM bracket onto the guides on the base.

Step 5

Push the CSM bracket firmly into place until the two release tabs are in their dropped position.

Step 6

Finally push the spine back into the base until you hear a click. The tab is back in position and the spine cannot move.

INSTALLATION INSTRUCTION

Copyright Prysmian Group - 2023 You may not copy, reprint, or reproduce in any form the content, either wholly or in part, of this Installation Guide, without the written permission of the copyright owner. Specifications are for product as supplied by Prysmian Group; any modification or alteration afterwards of product may give different result. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend the information within this Installation Guide without prior notice. This Installation Guide may include inaccuracies, omissions of content and of information and is not contractually valid unless specifically authorised by Prysmian Group. Property of Prysmian Group UK - Uncontrolled when printed Prysmian Cables & Systems Limited, Chickenhall Lane, Eastleigh, Hampshire, SO50 6YU, United Kingdom.

PRYSMIAN HELPLINE: + 44 (0) 78161916333
connectivity.help@prysmiangroup.com

Contact information

	Office	Telephone Fax	email
ASEAN	Singapore	T : +65 6898 3633 T : +65 6265 0707	sales.asean@prysmiangroup.com
AUSTRALIA	Liverpool	T: 1300 300 304 F : 1300 300 307	sales.telecom.au@prysmiangroup.com
CHINA	Wuxi	T : +86 510 68069518 F: +86 510 68069559	tls.china@prysmiangroup.com
DANUBIAN	Slatina	T : +40-349-406.628 F : +40-349-433.484	customercare.romania@prysmiangroup.com
FRANCE	Champs-Sur-Marne	T : +33 1 69 67 72 80	telecom.fr@prysmiangroup.com
ITALIA	Milano	T: +3964493939 F: +3964499264	pqa@prysmiangroup.com
LATAM	Sorocaba	T: +55 15 3212 6801 F: +55 15 3212 6814	sales.telecom.br@prysmiangroup.com
MIDDLE EAST	Dubai	T : +971 4 368 8682 F : +971 4 368 8683	dubaioffice@prysmiancables-me.com
NORDICS	Malmö	T : +46 380 554 265	info.nordic@prysmiangroup.com
NORTH AMERICA	Lexington	T : 800 669 0808	comm.cables@prysmiangroup.com
OPGW & SPECIALS	Vilanova	T: +34 93 811 6181 F: + 34 93 811 6031	opgw@prysmiangroup.com
RUSSIA	Moscow	T: +7 495 777 80 86 F: +7 495 777 80 89	info.ru@prysmiangroup.com
SPAIN & AFRICA	Maliaño	T: +34 942247118 F: +34 942247114	santander.bo@prysmiangroup.com
TURKEY	Istanbul		tpks@prysmiangroup.com
UK	Eastleigh	T: +44 2380 295 000	sales.telecom.uk@prysmiangroup.com