

IFSIT Cable And Wall Box Installation Guides

IP/Installation Procedure for IFSIT

This instruction details the installation procedure to mount the Indoor Flat Self Installed Transparent cable routing system.

The IFSIT cable kit allows you to discreetly run up to 2 fibres inside internal premise when no available embedded duct is available.



Precautions and Warnings

- ! This guide is only valid for products purchased from or approved by Prysmian.
- ! During this procedure all local Health & Safety statutory regulations must be adhered to.
- ! This installation should only be carried out by suitably trained competent persons.

Tools Required

1. Drill	2. Rubber Mallet	12 mm diameter Drill Bit, 25 cm long	4. Tape Measure	5. Spirit Level	6. Pencil
					

Parts List

IFSIT Cable 1fo or 2fo with either G.657.B3 or G.657.A2, supplied preterminated or not, installed on a cardboard reel	90° Flat Bend Accessory (Transparent) – 6 pcs	Installation Accessory – 1 pc	Through Wall Accessories (Transparent) – 2 pcs	Cardboard Dispenser
			 Corner side. Flat surface side.	 Up to 30m Up to 100m

Parts List

90° Bend Accessories (Transparent) – 6 pcs	Pass Wall Stick – 1 pc	Stripping Tool – 1 pc (Optional)
		

Installing the IFSIT on a Surface

Step 1



Before installing the IFSIT on any surface, it is mandatory to clean the surface properly to minimize the presence of dust.

BEST PRACTICE:

It is recommended to use a dust-catcher cloth or a brush.

Installing the IFSIT on a Surface

Step 2



Please plan your installation well in advance to avoid removing and reinstalling the IFSIT cable. Plan the route, align the cable, mark it and measure the distance.

Installing the IFSIT on a Surface

Step 3



Use a spirit level, lightly mark a straight line on the wall with a pencil.

Installing the IFSIT on a Surface

Step 4



Before installing, remove the cardboard reel from the box, to take off the protective band.

Installing the IFSIT on a Surface

Step 5



Remove all the kits from the Cardboard Reel.

Installing the IFSIT on a Surface



Step 6



To use the dispenser, remove two tabs for easy access to the cable.

Installing the IFSIT on a Surface

Step 7




Carefully lay the IFSIT on the surface. When in place, firmly push it at the wall. When secured, start using Installation Accessory.

BEST PRACTICE:

Repeat the process few times to ensure that the cable is secure.

Installing the IFSIT on a Surface

Step 8



Then take off the protective liner to carry on installing IFSIT.

BEST PRACTICE:

Due to extremely sticky nature of the tape, always remove 200mm protective lining at a time. IFSIT is prone to tangle if longer lengths of protective lining are removed at once.

Installing IFSIT around a Flat Corner using 90° Flat Bend Accessory

Step 1



To correctly maneuver the IFSIT cable around a corner, please use 90° Flat Bend Accessory.

Installing IFSIT around a Flat Corner using 90° Flat Bend Accessory


Step 2



Take off the protective liner and install 90° Flat Bend Accessory appropriately, in the desired location.

Installing IFSIT around a Flat Corner using 90° Flat Bend Accessory

Step 3



When installing the IFSIT into the 90° accessory, ensure that the cable is rotated onto its side. The product is designed like this to minimize strain on the cable.

Installing IFSIT around a Flat Corner using 90° Flat Bend Accessory

Step 4



To continue installation after 90° Flat Bend Accessory, simply follow IFSIT Installation steps in section 1 above.

Through Wall Accessories

Step 1



When installing IFSIT between rooms, use 12mm drill bit.

Through Wall Accessories

Step 2





Push Through Wall Accessories into the wall. And repeat for both sides of the wall.

Use rubber mallet if needed.

Through Wall Accessories


Step 3



When using pre-connectorised IFSIT cable, push the connector through the wall using the Pass Wall Stick, before installing the Through Wall Accessory.

Through Wall Accessories

Step 4





Post the IFSIT through the wall using the Pass Wall Stick. Before attaching the cable, plan the route, align the cable and measure the distance.

BEST PRACTICE

Start installation on the connector side to avoid unwanted IFSIT excess.

Through Wall Accessories


Step 5



After routing IFSIT along one side of the wall, stop about 150 mm from the hole and take off the protective liner. Remove only the amount of the protective liner necessary to put through the opposite side.

Through Wall Accessories

Step 6



Rotate the cable onto its side and slide into Through Wall Accessory.

Through Wall Accessories

Step 7



When cable is in place, firmly push it at the wall. When secured, start using Installation Accessory.

Through Wall Accessories

Step 8



Push in the Wall Accessory and repeat at the other side of the wall.

Through Wall Accessories

Step 9



Continue with the installation.

Stripping the IFSIT– without the IFSIT Stripping Tool

Step 1



The IFSIT cable is designed to have a middle parting to the centre of the cable which can be cut across.

To begin, locate this groove.

Stripping the IFSIT– without the IFSIT Stripping Tool


Step 2



Then using scissors, cut roughly 40mm down this groove.

Stripping the IFSIT– without the IFSIT Stripping Tool

Step 3



After cutting, use hands to gently grip either sheath leg and pull them apart to strip the sheath further.

Continue this until the desired amount of cable has been stripped.

Stripping the IFSIT– without the IFSIT Stripping Tool

Step 4



Once you have stripped the cable to your desired length, then gently remove the 900 μ fibre from the cable.

The best method is to peel it away from the top of the cable.

Stripping the IFSIT- without the IFSIT Stripping Tool


Step 5



Then proceed to cut the excess sheath and strip this cable like any other fibre cable.

Stripping the IFSIT– with the IFSIT Stripping Tool

Step 1




Firstly, remove all the adhesive from the IFSIT cable.

The easiest method of to run your thumb over the adhesive, and this causes it to roll away from the cable.

Stripping the IFSIT- with the IFSIT Stripping Tool

Step 2



Then place the IFSIT Stripping Tool on the cable where you would like to begin stripping.

Stripping the IFSIT- with the IFSIT Stripping Tool


Step 3



Put pressure on the IFSIT Stripping Tool to ensure that the blades, within the tool, can score the IFSIT Cable. After pressure is applied, guide the tool down the cable to score the entire cable.

Stripping the IFSIT- with the IFSIT Stripping Tool


Step 4



Once you have scored the cable, use scissors to cut down the cable on either side of the fibre and pull the sheath legs apart, to expose the fibre.

Stripping the IFSIT- with the IFSIT Stripping Tool

Step 5



Then proceed to cut the excess sheath and strip this cable like any other fibre cable.

Optical Test

Step 1



A final optical test must be carried out to ensure connectivity across the installation.

Contact information

	Office	Telephone/Fax	Email
ASEAN	Singapore	T : +65 6898 3633 T : +65 6265 0707	sales.asean@prysmian.com
AUSTRALIA	Liverpool	T: 1300 300 304 F : 1300 300 307	sales.telecom.au@prysmian.com
CHINA	Wuxi	T : +86 510 68069518 F: +86 510 68069559	tls.china@prysmian.com
DANUBIAN	Slatina	T : +40-349-406.628 F : +40-349-433.484	customercare.romania@prysmian.com
FRANCE	Champs-Sur-Marne	T : +33 1 69 67 72 80	telecom.fr@prysmian.com
ITALIA	Milano	T: +3964493939 F: +3964499264	pqa@prysmian.com
LATAM	Sorocaba	T: +55 15 3212 6801 F: +55 15 3212 6814	sales.telecom.br@prysmian.com
MIDDLE EAST	Dubai	T : +971 4 368 8682 F : +971 4 368 8683	dubaioffice@prysmiancables-me.com
NORDICS	Malmö	T : +46 380 554 265	info.nordic@prysmian.com
NORTH AMERICA	Lexington	T : 800 669 0808	comm.cables@prysmian.com
OPGW & SPECIALS	Vilanova	T: +34 93 811 6181 F: + 34 93 811 6031	opgw@prysmian.com
RUSSIA	Moscow	T: +7 495 777 80 86 F: +7 495 777 80 89	info.ru@prysmian.com
SPAIN & AFRICA	Maliaño	T: +34 942247118 F: +34 942247114	santander.bo@prysmian.com
TURKEY	Istanbul		tpks@prysmian.com
UK	Eastleigh	T: +44 2380 295 000	sales.telecom.uk@prysmian.com

Copyright Prysmian - 2025 You may not copy, reprint, or reproduce in any form the content, either wholly or in part, of this Installation Guide, without the written permission of the copyright owner. Specifications are for product as supplied by Prysmian: any modification or alteration afterwards of product may give different result. The information is believed to be correct at the time of issue. Prysmian reserves the right to amend the information within this Installation Guide without prior notice. This Installation Guide may include inaccuracies, omissions of content and of information and is not contractually valid unless specifically authorised by Prysmian. Property of Prysmian UK - Uncontrolled when printed Prysmian Cables & Systems Limited, Chickenhall Lane, Eastleigh,

PRYSMIAN HELPLINE: + 44 (0) 7816191633
connectivity.helpline@prysmian.com