Draka UC

Draka UC Connectivity

Universal Cabling System

Draka Single Gang Bevelled Euro Size Faceplate 86mm x 86mm - White

Part Number - YFPBP03647



Overview

- o Plastic Free Eco-Packaging Pack of 6
- Single Gang Bevelled Euro wall faceplate
- o Supplied with x2 fixing screws
- Up to 2 Euro modules/keystone adaptors with jacks
- o White

Product Description

Draka Single Gang Bevelled Faceplates with a 50mm x 50mm aperture opening accept x2 standard 25x50mm Euro type modules, or keystone adapters for use in conjunction with the Draka Cat5e/Cat6/Cat6a keystone jacks. The Draka Single Gang Bevelled Faceplate can also be assembled with our range of Blanking plates which are available in half/quarter sizes to fill opening spaces when not in use.

Draka Bevelled Faceplates are also available in Double Gang 146mm x 86mm with a 100 x 50 aperture opening for x4 standard 25mm x 50mm Euro type modules, or keystone adapters for use in conjunction with the Draka Cat5e/Cat6/Cat6a keystone jacks.

Product Specification

| Faceplate Material | Plastic ABS, UL94HB |
|--------------------|---------------------|
| Temperature Range | -10°C to 60°C |
| Colour | White RAL 9003 |
| Fastening | Screw Type |
| Surface | Bevelled |
| Width x Height | 86mm x 86mm |

© PRYSMIAN GROUP 2020, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian. The information is believed to be correct at the time of issue. Prysmian reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian.



Draka UC

Draka UC Connectivity


Universal Cabling System

| Aperture Size | 50mm x 50mm |
|---------------|-------------|
| No of units | 2 |


Standards Complied

| BSEN 60670-1:2005 + A1:2013 | Boxes and enclosures for electrical accessories for household and similar fixed electrical installations general requirements |
|-----------------------------|--|
| BSEN 61340-5-1:2007 | Protection of electronic devices from electrostatic phenomena. General requirements apply to activities that: manufacture, process, assemble, install, package, label, service, test, inspect, transport or otherwise handle electrical or electronic parts, assemblies and equipment susceptible to damage by electrostatic discharges greater than or equal to 100 V human body model (HBM). |
| RoHS | Restriction of Hazardous Substances Directive 2011/65/EU & 2015/863/EU |
| REACH | Regulation (EC) No 1907/2006 - Registration, Evaluation, Authorisation and Restriction of Chemicals EC1907/2006 |

Product Drawing







© PRYSMIAN GROUP 2020, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian. The information is believed to be correct at the time of issue. Prysmian reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian.

