

Draka UC Connectivity

Draka Angled Shutter for Keystone Jacks 25mm x 38mm – White

Part Number - YAABP03118



Overview

- Plastic Free Eco-Packaging – Pack of 24
- Mounts Draka keystone jacks into floor boxes or wall faceplates
- Compatible with all Draka UC keystone jacks
- Labelling field with clear protective cover
- Angled design optimises space in back box whilst ensuring minimal stress to installed cables

Product Description

Draka Angled Shutters fit the standard 25mm x 38mm LJ6C type openings on floor boxes and is compatible with all the keystone jack modules in the Draka Universal Cabling System portfolio. The adaptor has a spring-loaded shutter to protect the RJ45 port when not connected with a patch cord and comes with write-on label with clear protective window for port identification.

Draka Angled Shutters are available in the Euro 25 x 50mm and 6C (LJ6C) 25 x 38mm sizes. Blanking plates are available in half size for LJ6C 25mm x 38mm size to configure single or triple outlets.

Product Specification

| | |
|-------------------------|---------------------|
| Angled Adapter Material | Plastic ABS, UL94HB |
| Temperature Range | -10°C to 60°C |
| Colour | White RAL 9003 |
| Fastening | Engage (snap) |
| Surface | Angled |
| Width | 25mm |
| Height | 38mm |

© PRYSMIAN GROUP 2020, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian. The information is believed to be correct at the time of issue. Prysmian reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian.

Standards Complied


| | |
|------------------------------------|--|
| BSEN 60670-1:2005 + A1:2013 | Boxes and enclosures for electrical accessories for household and similar fixed electrical installations general requirements |
| BSEN 61340-5-1:2007 | Protection of electronic devices from electrostatic phenomena. General requirements apply to activities that: manufacture, process, assemble, install, package, label, service, test, inspect, transport or otherwise handle electrical or electronic parts, assemblies and equipment susceptible to damage by electrostatic discharges greater than or equal to 100 V human body model (HBM). |
| RoHS | Restriction of Hazardous Substances Directive 2011/65/EU & 2015/863/EU |
| REACH | Regulation (EC) No 1907/2006 - Registration, Evaluation, Authorisation and Restriction of Chemicals EC1907/2006 |

© PRYSMIAN GROUP 2020, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian. The information is believed to be correct at the time of issue. Prysmian reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian.

Product Drawing



© PRYSMIAN GROUP 2020, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian. The information is believed to be correct at the time of issue. Prysmian reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian.