

OPTITAP PRECONNECTORISED DROP CABLE® prysmian

Product Design

Product code – see tables below



DESIGN & CONSTRUCTION

- The cables are supplied in a coil.
- Terminated with an SC or LC or MPO hardened fibre optic connector (HFOC).
- The cable assembly can be equipped with only one connector at one end, or one connector at both ends.
- Available in a range of lengths from 30M to 500M.
- A range of cable constructions can be used.
- OptiTap®-drop cable.

PRODUCT DESCRIPTION

The Preconnectorised OptiTap®- drop cables are available in various lengths using various cable designs to suit the local market. A variety of connector options are available, including Hardened MPO, LC and SC (OptiTap®-drop cable). Either cable ends can be pre-terminated with hardened connector solutions or standard connectors (SC or LC or MPO).

Connector Specifications - Technical data

Hardened Connectors



Standard Connectors




Connector Type	Insertion Loss	Return Loss	Insertion Loss	Return Loss
SC/APC	0.3 dB	60 dB	0.3 dB	60 dB
LC/APC	0.3 dB	60 dB	0.3 dB	60 dB
MPO	0.35 dB	60 dB	0.35 dB	60 dB

OPTITAP PRECONNECTORISED DROP CABLE®

Cable Design

HDPE 5mm OD round cable




Cable

- **Fibre Type:** single mode G.657A2, 250um fibre optic.
- **Central Tube:** PBT, white.
- **Reinforcement:** Aramid + water resistant glass yarn.
- **Strength Member:** GRP (Glass-fibre Reinforced Polymer).
- **Sheath:** Black UV resistant HDPE.

Technical data

No. of Fibres		1		4	
Loose Tube - Ø	mm	1.5 ± 0.2		2.2 ± 0.2	
Cable Diameter	mm	5.0 ± 0.3			
Cable Weight	Kg/km	27 ± 5			
Minimum Bending Radius	mm	Static 10 x Cable-Ø		Dynamic 20 x Cable-Ø	
Temperature Range	°C	Installation - 5 to + 60	Transport & Storage - 40 to + 70		Operation - 25 to + 70

LSZH 5mm OD round cable



Cable

- **Fibre Type:** single mode G.657A2.
- **Loose Tube:** PBT, white.
- **Ripcord:** Aramid or Polyester
- **Reinforcement:** Aramid + water resistant yarn.
- **Sheath:** Black UV resistant LSZH.

Technical data

No. of Fibres		1		
Loose Tube - Ø	mm	2.0 ± 0.2		
Cable Diameter	mm	5.0 ± 0.3		
Cable Weight	Kg/km	30 ± 5		
Minimum Bending Radius	mm	Static 10 x Cable-Ø		
Temperature Range	°C	Installation - 5 to + 60	Transport & Storage - 40 to + 70	Operation - 25 to + 70

OPTITAP PRECONNECTORISED DROP CABLE[®]



Part Numbers

Part Number	Length	Cable Type	Connector 1	Connector 2
XPCSC02655	10M \pm 3%	HDPE 5mm 1FO	OptiTap®	None
XPCSC02536	35M \pm 3%	HDPE 5mm 1FO	OptiTap®	None
XPCSC02656	50M \pm 3%	HDPE 5mm 1FO	OptiTap®	None
XPCSC02537	65M \pm 3%	HDPE 5mm 1FO	OptiTap®	None
XPCSC02657	100M \pm 3%	HDPE 5mm 1FO	OptiTap®	None
XPCSC02538	105M \pm 3%	HDPE 5mm 1FO	OptiTap®	None
XPCSC02658	150M \pm 3%	HDPE 5mm 1FO	OptiTap®	None
XPCSC02539	160M \pm 3%	HDPE 5mm 1FO	OptiTap®	None
XPCSC02540	200M \pm 3%	HDPE 5mm 1FO	OptiTap®	None
XPCSC02659	250M \pm 3%	HDPE 5mm 1FO	OptiTap®	None
XPCSC02541	350M \pm 3%	HDPE 5mm 1FO	OptiTap®	None

© PRYSMIAN GROUP 2024, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian. The information is believed to be correct at the time of issue. Prysmian reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian.