


Prysmian UC400 Cat.6 U/UTP SD PE OUTDOOR

U/UTP Installation cable



Application

Primary (Campus), Secondary (Riser), Tertiary (Horizontal)
IEEE 802.3: 10Base-T; 100Base-T; 1000Base-T;
IEEE 802.5 16 MB; ISDN; TPDDI; ATM
Power over Ethernet (PoE) / Type 1-4

Standards

EIA/TIA 568.2-D
ISO/IEC 11801 2nd ed; IEC 61156-5;
EN 50173-1, EN 50288-6-1
IEEE 802.3af / at / bt

Construction

Conductor	Bare copper AWG24
Insulation	Polyethylene, Ø 0.95 mm nom
Twisting	2 cores to the pair
Cable lay up	4 pairs to the core non-metallic cross separator (spline)
Sheath	PE, black, for outdoor installation

Mechanical properties

Minimum bending radius	Installation	8 x D
	Installed	4 x D
Temperature range	during operation	-20°C up to + 60°C
	during installation	0°C up to + 50°C

Prysmian UC400 Cat.6 U/UTP SD PE OUTDOOR

Electrical properties

at 20°C

DC loop resistance	188 Ω /km
Resistance unbalance	$\leq 2\%$
Insulation resistance (500 V)	$\geq 5000 \text{ M}\Omega \cdot \text{km}$
Capacitance at 800 Hz	Nom. 48 nF/km
Capacitance unbalance (pair to ground)	$\leq 1500 \text{ pF/km}$
Mean impedance 100 MHz	$100 \pm 5 \Omega$
Nominal velocity of propagation	Approx. 67 %
Propagation delay	Nominal 518 ns/100m
Delay skew	Nominal 20 ns/100m
Test voltage (DC, 1 min)	1000 V
Core/Core	
Coupling attenuation	40dB

Electrical data (nominal)

acc. to Cat.6 (at 20°C)

f	Attenuation		NEXT		PS-NEXT		ACR		PS-ACR		ELFEXT		PS-ELFEXT		Return loss	
(MHz)	(dB/100m)		(dB)		(dB)		(dB/100m)		(dB/100m)		(dB/100m)		(dB/100m)		(dB)	
	max.	Nom.	min.	nom.	min.	Nom.	Min.	Nom.	Min.	Nom.	min.	Nom.	min.	Nom.	min.	Nom.
1	2.1	1.9	74	78	72	75	72.0	76.1	70.0	73.1	68	82	65	80	20	22
4	3.8	3.8	65	69	63	66	61.2	65.2	59.2	62.2	56	70	53	68	23	25
10	6.0	6.0	59	63	57	60	53.0	57.0	51.0	54.0	48	62	45	60	25	27
16	7.6	7.6	56	60	54	57	48.4	52.3	46.4	49.3	44	58	41	56	25	27
20	8.5	8.5	55	59	53	56	46.5	50.0	44.5	47.0	42	56	39	54	25	27
31.2	10.7	10.7	52	56	50	53	41.3	45.0	39.3	42.0	38	52	35	50	23.6	26
62.5	15.5	15.1	47	51	45	48	31.5	36.0	29.5	33.0	32	46	29	44	21.5	24
100	19.9	19.1	44	48	42	45	24.1	28.9	22.1	25.9	28	42	25	40	20.1	23
125	22.5	21.3	43	47	41	44	20.5	25.2	18.5	22.2	26	40	23	38	19.5	22
155.5	25.4	23.8	42	45	40	42	16.6	21.3	14.6	18.3	24	38	21	36	18.8	21
175	27.1	25.3	41	44	39	41	13.9	19.1	11.9	16.1	23	37	20	35	18.4	21
200	29.2	27.0	40	44	38	41	10.8	16.5	8.8	13.5	22	36	19	34	18.0	20
250	33.0	32.0	38	42	36	39	5.0	10.0	2.0	7.0	20	34	17	32	17.3	19
300		36.1		41		38		4.8		1.8		32		30		19
400		41.7		39		36		-2.7		-5.7		30		28		18

Prysmian UC400 Cat.6 U/UTP SD PE OUTDOOR

Technical data

Product Reference Code	Product name	Outer diameter mm	Weight kg/km	Copper index	Tensile force N
60109956	Prysmian UC400 C6 U/UTP SD PE OUTDOOR 305BR	5.2	32	18.0	80