

Draka UC Connectivity

Draka Cat6a Screened 1U/19" 24Port Angled Modular Keystone Panel

Part Number – YPPBP03337



Overview

- Plastic Free Eco-Packaging – Pack of 1
- Supplied with Cage nuts/Screws & Nylon ties
- Metal Cable Management Support Bar
- Earth/Grounding cable included
- Fast fit rear cable management
- For use with Cat6a STP Jack YMJB03208

Product Description

Draka Angled Screened Modular Patch Panels are designed for use with Draka Cat6a STP keystone jacks. Each panel is supplied with a rear metal cable management support bar to provide a solid and strong support to relieve cable stresses. The panel has screen printed port numbers with write on description labels for port identification, protected by a transparent cover for fast and easy labeling on site. The modular panel features a nickel-plated plate to provide grounding continuity between connectors and panel. For standards compliance to BS EN 50310 and BS EN 50174-1, the panel is provided with an earth grounding cable pre-connected, to enable quick bonding/grounding within your telecommunications rack/enclosure.

Product Specification

| | |
|--|--------------|
| Suitable for number of outlets / modules | 24 |
| Category | Cat6A |
| Number of rack units | 1U |
| Panel material | SPCC |
| Colour | Black |
| Mounting type | 19" mounting |

© PRYSMIAN GROUP 2020, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian. The information is believed to be correct at the time of issue. Prysmian reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian.

| | |
|---------------|--|
| Height | 44.45mm |
| Width | 482.27mm |
| Depth | 206.75mm with Management bar installed |

Standards Complied





| | |
|-------------------------|---|
| ANSI/EIA-310-D | Electronic Industries Association standard for horizontal spacing, vertical hole spacing, rack opening and front panel width |
| IEC 60297-3-100 | Mechanical structures for electronic equipment - Dimensions of mechanical structures of the 482,6 mm (19 in) series - Part 3-100: Basic dimensions of front panels, subracks, chassis, racks and cabinets |
| BS EN 50310:2016 | Telecommunications bonding networks for buildings and other structures |
| IEC 60603-7 | Connectors for electronic equipment - Part 7: Detail specification for 8-way, unshielded, free and fixed connectors |
| RoHS | Restriction of Hazardous Substances Directive 2011/65/EU & 2015/863/EU |
| REACH | Regulation (EC) No 1907/2006 - Registration, Evaluation, Authorisation and Restriction of Chemicals EC1907/2006 |

© PRYSMIAN GROUP 2020, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian. The information is believed to be correct at the time of issue. Prysmian reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian.

Product Drawings



© PRYSMIAN GROUP 2020, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian. The information is believed to be correct at the time of issue. Prysmian reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian.