

**OAsys® INTERNAL PLANT
INTERNAL CSP**
Part Number: XCPSC00291-297

Description

- The OAsys Internal Customer Splice Box is designed for use in residential, small and large businesses premises. The unit houses a single splice tray and allows fibres from internal or external cables to be spliced to pigtails for connection to the optical network unit.

Tools Required:

Pozidrive Screwdriver, Mallet, 14mm Socket Driver, Cable Stripping tools, Fibre stripping tools, Splicing machine, drill, 6mm drill bit.

Tools & Additional Items Required






Additional Items Required: **Prysmian Part No.**

None

Optional Items: **Prysmian Part No.**

| | |
|---------------------|--------------------|
| Resin Pack | XPESC00054 |
| Security Screws | XAGSC00476 |
| Gas Block Connector | XAGSC00404 |
| Patch Cords | Contact Sales Desk |


Component Parts (pictures not to scale)

| | | |
|---|--|--|
| <p>1 Internal CSP + Fixings Qty 1</p>  | <p>2 Splice Protectors Qty 4, 8 or 12</p>  | <p>3 Cable Gland Qty 1</p>  |
| <p>4 Cable Funnel Qty 1</p>  | <p>5 Compound 16 Qty 1</p>  | <p>6 Transport Tube Qty 1</p>  |

Prysmian
Group
INSTALLATION INSTRUCTION

Box Preparation and Mounting


Step 1



- Using a 14mm Socket Driver and a Mallet, knock out the cable entry port on the right-hand side of the box. Take care to support the box properly when doing this.

Box Preparation and Mounting

Step 2



- If the input cable is between 8mm and 15mm in diameter, and does not require water/gas blocking, insert the Cable Gland (3) through the port and secure into place by fully tightening the lock nut on the inside of the box.
- If the cable is over 15mm in diameter (up to 20mm), or water/gas blocking is required between the cable elements, insert the funnel (4) through the port of the box. Secure the funnel to the box using the lock nut supplied with the Cable Gland (3).

Box Preparation and Mounting

Step 3



- Identify a suitable mounting position for the box.
- Mark the position of the four fixing holes for the box.
- Drill the four fixing holes using a 6mm drill bit.

Prysmian
Group
INSTALLATION INSTRUCTION

Box Preparation and Mounting


Step 4



- Fix the box to the wall using the fixing screws provided.

Cable Installation


Step 5



- At the outside wall, mark a butt position on the input cable level with the top of the cable gland. Allow a further 2 metres for the jointing allowance for conventional cables and a further 200mm for a Blown Fibre cable.

Cable Installation


Step 6



- Strip the cable sheath to expose the cable elements and remove any tapes or binders.
- For conventional cables, cut the central strength member to 50mm in length.
- Remove the sheath from the strength member back 10mm.

Cable Installation

Step 7




- Insert the cable through the gland and locate the strength member into the strength member retaining clamp. Fully tighten the grub screw to lock the cable into place.
- Fully tighten the Cable Gland **(3)** to seal and anchor the cable to the box.

Prysmian
Group
INSTALLATION INSTRUCTION

Cable Installation

Step 8




- Strip the cable element to expose the fibres approximately 30mm from the cable butt.
- Over sleeve the cable element with the transport tube and feed the fibres through the 5mm tube connector onto the splice tray.
- Push the tube into the connector. Ensure the tube is routed around the guide and pushed into the grip as shown.

Prysmian
Group
INSTALLATION INSTRUCTION

Cable Installation

Step 9

Fit gas block connector if required




- For Blown Fibre Cables, ensure that the Blown Fibre tube is cut 175mm from the cable butt.
- If gas blocking is required between the tube and the fibres, replace the 5-5mm tube connector with a 5mm Gas Block Connector (Part Number XAGSC00404).

Prysmian
Group
INSTALLATION INSTRUCTION

Cable Installation

Step 10


Fit gas block connector if required



- Route the tube around the guide and plug it into the 5mm connector.
- Ensure the tube is routed around the guide and is pushed into the retaining grip.
- Install the fibre using approved practices.

Connection of Drop Cables


Step 11



- Splice the fibres to the pigtail fibres already stored on the splice tray. The colour sequence can be seen in the following step.
- Place the splice protectors (2) in the bays and route the fibres around the tracks, storing and coiling them beneath the tabs of the central storage area.

Connection of Drop Cables

Step 12




| Adaptor No. | Pigtail Colour |
|--------------------|-----------------------|
| 1 | Red |
| 2 | Blue |
| 3 | Green |
| 4 | Yellow |
| 5 | Violet |
| 6 | White |
| 7 | Grey |
| 8 | Orange |
| 9 | Brown |
| 10 | Black |
| 11 | Turquoise |
| 12 | Pink |

Fibre colour sequence

Connection of Drop Cables


Step 13



- If the funnel has been used and water/gas blocking is required, use the Compound 16 (5) at the bottom of the funnel to temporarily seal between the cable and the funnel.
- Fill the funnel with resin (supplied separately – Part No. XPESC00054) to seal the cable. Allow 15 minutes for the resin to set.

Connection of Drop Cables


Step 14



- Fit the protection Cover supplied with the Internal CSP by sliding the two rails into the slots on the bottom of the box.

Connection of Drop Cables

Step 15



- Replace the cover of the box and secure by tightening the four screws.



Clean before you connect.

It is important that all fibre connectors and adapters are cleaned prior to mating using approved local practice. Failure to clean may result in either poor signal performance and/or permanent damage to the connector end faces.

Copyright Prysmian Group - 2022 You may not copy, reprint, or reproduce in any form the content, either wholly or in part, of this Installation Guide, without the written permission of the copyright owner. Specifications are for product as supplied by Prysmian Group: any modification or alteration afterwards of product may give different result. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend the information within this Installation Guide without prior notice. This Installation Guide may include inaccuracies, omissions of content and of information and is not contractually valid unless specifically authorised by Prysmian Group. Property of Prysmian Group UK - Uncontrolled when printed Prysmian Cables & Systems Limited, Chickenhall Lane, Eastleigh, Hampshire, SO50 6YU, United Kingdom.

PRYSMIAN HELPLINE: + 44 (0) 78161916333
connectivity.help@prysmiangroup.com

Page 16 of 16