

MECH SEAL – CIRCULAR 20-23mm GLAND INSTALLATION GUIDE

KIT CONTENTS

ITEM No.:	DESCRIPTION	QTY
1	LARGE BODY SEALING GLAND	x1
2	LARGE NUT	x1
3	O-RING BS124 NITRILE	x2
4	STRENGTH MEMBER RETENTION BRACKET	x1
5	STRENGTH MEMBER RETENTION BOSS	x1
6	GRUB SCREW	x1
7	M4 x 12mm CSK POZI PAN SCREW	x1
8	20-23mm SINGLE WAY CABLE SEAL	x1
9	ANTI-TORSION CLAMPS LARGE	x1
10	JUBILEE CLIP 16 - 27mm – LARGE	x1
11	SPACERS	x4
12	GREASE SACHET	x1



MECH SEAL – CIRCULAR 20-23mm GLAND INSTALLATION GUIDE

Step 1

REMOVE PORT BLANK FROM BASE BY FULLY SQUEEZING TOGETHER THE TABS FROM INSIDE THE BASE.

NOTE: YOU MAY NEED TO ROTATE THE BLANK IN THE PORT TO SQUEEZE THE TABS.

USING YOUR OTHER HAND OR PLIERS, HOLD THE CENTRAL RIB AND FIRMLY PULL UNTIL THE PORT BLANK IS RELEASED.



MECH SEAL – CIRCULAR 20-23mm GLAND INSTALLATION GUIDE

Step 2


IDENTIFY THE CABLE DIAMETER AND USING THE TABLE BELOW SELECT THE CORRECT NUMBER OF SPACERS REQUIRED.

CABLE \varnothing	SEAL SIZE (8)	CABLE RANGE	SPACERS (11)
20mm – 22.9mm	20-23mm SEAL XJTSG02051	20-20.9mm	2
		21-21.9mm	3
		22-22.9mm	4

MECH SEAL – CIRCULAR 20-23mm GLAND INSTALLATION GUIDE

Step 3


REMOVE THE MEDIUM NUT (2) FROM THE GLAND ASSEMBLY AND INSERT THE ANTI-TORSION CLAMP (9) AS SHOWN BELOW.



MECH SEAL – CIRCULAR 20-23mm GLAND INSTALLATION GUIDE

Step 4

SLIDE THE JUBILEE CLIP (10) OVER THE CABLE END FIRST. THEN SLIDE THE MEDIUM NUT (2) AND ANTI-TORSION CLAMP (9) OVER THE CABLE END (FITTED TOGETHER).



MECH SEAL – CIRCULAR 20-23mm GLAND INSTALLATION GUIDE

Step 5

INSERT THE SEAL (8) INTO THE GLAND ASSEMBLY (1) AS SHOWN.



MECH SEAL – CIRCULAR 20-23mm GLAND INSTALLATION GUIDE

Step 6


FIT THE REQUIRED NUMBER OF SPACERS (11) OVER THE THREAD OF THE GLAND BODY ASSEMBLY (1).



MECH SEAL – CIRCULAR 20-23mm GLAND INSTALLATION GUIDE

Step 7

SLIDE THE GLAND ASSEMBLY (1) ONTO THE CABLE AND PUSH THROUGH APPROXIMATELY 2.2m OF CABLE. LOOSELY TIGHTEN THE MEDIUM NUT (2) BACK ONTO THE GLAND BODY AND LOOSELY TIGHTEN JUBILEE CLIP (10) ONTO THE ANTI-TORSION CLAMP (9).




MECH SEAL – CIRCULAR 20-23mm GLAND INSTALLATION GUIDE

Step 8

STRIP CABLE BACK 2m (S/M TM NODE) or 3m (L/XL TM NODE) EXPOSING THE ELEMENTS, GRP AND ARAMID YARN IF APPLICABLE.

MEASURE FROM THE CABLE BUTT AND CUT THE GRP TO 55mm AND CUT THE ARAMID YARN TO 170mm.


APPLY GREASE (12) ALONG CABLE SHEATH FROM THE BUTT BACK 200mm & PULL CABLE BACK UNTIL BUTT ENDS UP IN POSITION SHOWN.



MECH SEAL – CIRCULAR 20-23mm GLAND INSTALLATION GUIDE

Step 9


SLIDE RETENTION BOSS (5) OVER GRP AND LINE UP THE SCREW HOLE. SECURE RETENTION BOSS (5) TO THE RETENTION BRACKET (4) USING SCREW (7). ENSURE THE GROOVES LINE UP AT THE TOP. IF THE CABLE HAS ARAMID YARN SEE NOTE 10.



MECH SEAL – CIRCULAR 20-23mm GLAND INSTALLATION GUIDE

Step 10


IF THE CABLE HAS ARAMID, LOOSELY FASTEN THE RETENTION BOSS (5) USING THE SCREW (7) AND SEPARATE THE ARAMID FROM THE ELEMENTS. WRAP THE ARAMID YARN AROUND THE SCREW x2 TURNS AND FINISH THE SECOND TURN WITH THE ARAMID FACING OUT TO THE SIDE AS SHOWN BELOW AND TIGHTEN THE SCREW (7) TO THE RETENTION BOSS (5) USING A SCREWDRIVER. TRIM EXCESS ARAMID.



MECH SEAL – CIRCULAR 20-23mm GLAND INSTALLATION GUIDE

Step 11

TIGHTEN THE GRUB SCREW (6) ONTO THE GRP USING 2 mm ALLEN KEY. DO NOT OVER TIGHTEN.




MECH SEAL – CIRCULAR 20-23mm GLAND INSTALLATION GUIDE

Step 12

ENSURE THE SINGLE SEAL (8) IS FULLY INSERTED INTO GLAND BODY (1). LOCATE THE ANTI-TORSION CLAMP (9) NODULES AND PUSH THE CLAMP ONTO THE SEAL SO THE ANTI-TORSION CLAMP CANNOT ROTATE.

**NOTE: DO NOT FORCEFULLY ROTATE THE CLAMP.
IF THE ANTI-TORSION CLAMP ROTATES, IT HAS NOT BEEN
LOCATED CORRECTLY.**




MECH SEAL – CIRCULAR 20-23mm GLAND INSTALLATION GUIDE

Step 13

SLIDE THE MEDIUM NUT (2) OVER THE ANTI-TORSION CLAMP AND SCREW THE NUT DOWN UNTIL ALL THE SURFACES MATE. ENSURE THE ANTI-TORSION CLAMP STAYS LOCATED BY PUSHING DOWN ON THE END WHILST IN POSITION. USING JUBLIEE CLIP (10), SLIDE IT OVER THE END OF CLAMP AND TIGHTEN USING SCREWDRIVER.

NOTE: DO NOT OVER TIGHTEN ON CABLE.


APPLY 2 TURNS OF ELECTRICAL TAPE OVER THE JUBILEE CLIP.



MECH SEAL – CIRCULAR 20-23mm GLAND INSTALLATION GUIDE

Step 14

PUSH GLAND (1) INTO S/M/L/XL TM NODE BASE. ONCE RESISTANCE ON O-RING IS FELT, CONTINUE PUSHING WITH A TWISTING ACTION UNTIL AN AUDIBLE CLICK IS HEARD. VISUALLY CHECK FROM INSIDE THE BASE ALL 3 CLIPS ARE SECURED INTO BASE.



MECH SEAL – CIRCULAR 20-23mm GLAND INSTALLATION GUIDE

Step 15

INSERT THE CABLE TUBE INTO THE MANIFOLD RESTRAINT AND STRIP THE TUBE AT THE INDICATED POSITION, AS SHOWN. ROUTE ELEMENTS AND FIBRES AS PER THE CLOSURE INSTALLATION INSTRUCTIONS.

